This document was generated on 12/15/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0981721002

Status: Active - Custom

Description: 5.00mm (.197") NSCC Wire-to-Wire 2.80mm (.110") Receptacle Housing, With TPA™, 6 Circuits, Black



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	98172
Application	Power
Product Name	NSCC

Physical

Circuits (maximum)	6
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm (.197")
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	18A

Material Info

Country of Origin	BR, CN, DE, IE, SK

Reference - Drawing Numbers

Application Specification	RAS-98172-001
Packaging Specification	PP-98172

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
98172Series

Mates With
Harnessmaker specific

Use With
2.80mm (.110") UCC terminals (98898-series)

This document was generated on 12/15/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.