

MTFDKEL128THE-1BM15ATYY

Documents

+

RoHS

Specifications

Capacity	Speed
128GB	NSR
MT/s	Protocol
NSR	PCIE GEN4
Operating Temp	Pin Count
-40C to +105C	291-ball
Part Status Code	Dry Pack Qty



Package Dimension (W x L x H) mm

16.00 x 20.00 x 1.30

Tape & Reel Qty

1000

Package Type

GREEN

Technology

uSSD TLC

[Products](#)

[Markets & Industries](#)

[Partners](#)

[Sales & Support](#)

[About](#)

[Investor relations](#)

[CONTACT US](#)

[SALES SUPPORT CONTACT](#)

[TECHNICAL SUPPORT CONTACT](#)

[Legal](#)

[Micron privacy notice](#)

[Suppliers](#)

[Terms and conditions of sale](#)

[Careers](#)

[Your privacy choices](#)

©2025 Micron Technology, Inc. All rights reserved. Information, products, and/or specifications are subject to change without notice. All information is provided on an "AS IS" basis without warranties of any kind. Drawings may not be to scale. Micron, the Micron logo, and all other Micron trademarks are the property of Micron Technology, Inc. All other trademarks are the property of their respective owners.

