



Part Number : [1301510023](#)

Product Description : Super-Safeway Adapter
NEMA 5-15 Receptacle - Female End 15A/125V, NEMA
L5-20 Plug - Male End, 20A/125V

Series Number : 130151

Status : Active

Product Category : Wiring Devices

Engineering Part Number : 1740



Documents and Resources

Drawings

[1301510023_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771- DC (04 Feb 2026) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------------|--|
| Status | Active |
| Category | Wiring Devices |
| Series | 130151 |
| Description | Super-Safeway Adapter NEMA 5-15 Receptacle - Female End 15A/125V, NEMA L5-20 Plug - Male End, 20A/125V |
| IP Rating | N/A |
| NEMA Configuration | NEMA L5-20 |
| Product Name | Super-Safeway |
| Specialty | N/A |
| Type | Adapter |
| UPC | 78678875280 |

Agency

| | |
|-----|--------|
| CSA | LR6837 |
| UL | E10176 |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 60.0A |
| GFCI | No |
| Voltage - Maximum | 125V |

Physical

| | |
|-----------|-------------|
| Cord Type | N/A |
| Flange | No |
| Flip Lid | No |
| Gender | Male-Female |
| Length | N/A |

| | |
|-------------------|---------------|
| Lighted Connector | No |
| Locking Blade | Yes |
| Net Weight | 150.139/g |
| Poles | 2-pole/3-wire |
| Receptacle Type | N/A |

This document was generated on Apr 12, 2026