

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=H403505D00J0G* > H403505D00J0G

H403505D00J0G

H403505D00J0G - Terminal Blocks : pluggable plug with spring connection, 5.08mm pitch, with flange, hook on back side, 3 position



ACTIVE

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support
Sample request



Customer drawing



Product Environmental Compliance Report

Specifications

Download document

Mating Half

General Dimensional Electrical Physical Approvals / Certifications

General	
Gender	Female plug
Packaging	Box
Product Type	Spring Clamp Pluggable System
Series	H4
Number of Positions	3
Dimensional	
Strip length (Wire)	9 to 10 mm
Solid wire size (AWG)	12 to 26
Stranded wire size (AWG)	12 to 26
Pitch	5.08 mm
Electrical	
Withstanding Voltage	1.6 kV
Current rating	10 A
Voltage rating	300 V
Physical	
Color (Housing)	Green
Conductor entry angle	90°
Material (Housing)	Thermoplastic UL94V-0
Terminal material	Phosphor bronze
Terminal plating	Tin
Connection Type	Spring connection
Temperature (Operating - range)	-40 to 115 Celcius
Approvals / Certifications	
Approvals / Certifications	cULus

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.