

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search


Multi Selection Search

Search by category

HM2P70PDE121N9LF

HM2P70PDE121N9LF

HM2P70PDE121N9LF - Millipacs® : 2 mm Hard Metric Series
5 Row vertical Press-Fit Header, Type B 22 with 110 Signal
Pins and RoHS compatible



Customer drawing

Product Environmental Compliance Report

ACTIVE 48

RoHS Compliant

Distributor Stock

CORE RANGE

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Specifications

Download document

General Dimensional Electrical Mechanical Physical Approvals / Certifications Mounting Other Features	
General	
Gender	Header
Number of contacts	110
Number of rows	5
Orientation	Vertical
Product Type	Header
Series	Module Type B (22 Pos)
Shielded	Yes
Number of levels (Contact)	Refer to Customer Drawing
Dimensional	
Length (Tail)	Short Tail (3.7 mm)
Electrical	
Current rating	1.5A at 20°C, 1A at 70°C
Resistance (Contact)	20 milli ohms max.
Resistance (Insulation)	10,000 M-ohms min.
Voltage rating	750V rms
Mechanical	
Withdrawal Force	0.15N min. per Contact Pair
Hertz stress	200 Kpsi min.
Mating force (Signal)	0.75N max. per Contact Pair
Physical	
Material (Contact)	Copper alloy
Material (Housing)	Thermoplastic (UL94 V-0)
Temperature (Operating - range)	-55°C to +125°C
Approvals / Certifications	
Approvals / Certifications	UL Approved
UL File Number	E66906
Mounting	
Mounting style (Board)	Press-Fit
Other Features	
Packaging (Type)	Tray

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.