




DIMENSIONS



METHOD OF INSERTION
ON THE PCB = FLAT ROCK



P.C. CARD DRILLING
(Component side view)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000C

SPECIFICATION 759 = no contact in position : row:a-b-c cavities 6-7
OR SPECIFICATION CI =

European Views

rev	ecn no	dr	date
A	-	ROU	1998/03/06
B	LS05-004	JTA	2005/02/26
C	LS06-0095	LGO	2006/06/24
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	size A3	Scale 1.5
TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR	LINEAR	0.X ±0.1		
Dr	ROUILLARD	1998/03/06	0.XX ±0.1	0.XXX ±0.1	ECN	LS06-0095
Eng	TARON	1998/03/06	0.XX' ±2'	Product family	DIN 8609	Spec ref -
Chr	LEGARE	1998/03/06				
Appr	LEGARE	1998/03/06				
FCI		STANDARD FEMALE 3 ROW		C-8609-0695		Rev. C
42 CONTACTS		catalog no		CUSTOMER		sheet 1 of 1