Part Number : 2270232114
Product Description : Pre-Crimped Lead DuraClik Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black
Series Number : 227023
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2270232114_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	227023
Description	Pre-Crimped Lead DuraClik Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black
Application	Automotive, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	DuraClik Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	DuraClik
UPC	198282672425

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.614/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression

Downloaded from Arrow.com.

Wire/Cable Type	TPE Insulated Bare Copper
Wire Size (AWG)	22

Mates With / Use With

Use with Part(s)

Description	Part Number
DuraClik TPA Single Row Receptacle Housings	505151

Downloaded from Arrow.com.