


4802, Socket, PCB terminals, screened, 3.5 mm, 2-pole, straight, UK-Connector



Description

- PCB Mounting :
 - Screw-on mounting , from rear-side
- Data and Signal transfer
 - Data and Signal Connectors 2-pole , shielded , straight
- Reinforced gold plating for increased insertions

References

Alternative: Housing insulated 4802.2230
Last order date: 30.06.2016


Technical Data

Diameter	3.5 mm
Number of Poles	2-pole
Ratings DC	1 A / 12VDC
Ratings AC	1 A / 12VAC
Dielectric Strength	500VDC
Insulation Resistance	> 10000 MΩ @ 500VDC

Allowable Operation Temperature	-20 °C to 70 °C
Terminal	PCB terminals
Mounting	Screw-on mounting wall thickness max. 2.0mm
Housings	screened
Style	straight
Lifetime	10000 Insertions

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [General Product Information](#)

Dimensions



Diagrams



All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Data and Signal Plug/ Sockets	3.5	2-pole	PCB terminals	4802.2220

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit	100 Pcs
----------------	---------

PHASE OUT