

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
MINNEAPOLIS, MINNESOTA

FED. MFR. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BA-2RV

ABN7000

BA-2RV

PAGE 1 OF 1

M

DRAWING
NUMBER

10 X

ISSUE
12

BA-2RV
ISSUE 6

REPLACES

RELEASE NO.

CHECK

18 JAN 06

18 JAN 73

10 JUN 94

25 AUG 98

20 SEP 99

18 JAN 06


12 JAN 62

12 JAN 62

12 JAN 62

12 JAN 62

12 JAN 62



NOTE
MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 2 1/2 OZ MAX

RELEASE FORCE ----- 1/2 OZ MIN

PRETRAVEL ----- .625 MAX

DIFFERENTIAL TRAVEL ----- .109 MAX

OVERTRAVEL ----- .078 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L23

20A - 125, 250 OR 480 VAC

10A - 125 VAC "L"

1HP - 125 VAC, 2HP - 250 VAC

1/2A - 125 VDC, 1/4A - 250 VDC

L288

L308

L315

CE 05 RU SA
20(3)A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT

FORMTEK

FG-50378

DRAWN

12 JAN 62

12 JAN 62

12 JAN 62