

# 171506-3 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

## Ring and Spade Tongue Terminals

PIDG RING (22-18)  
**171506-3** ✔  
TE Internal Number: 171506-3

**Product Highlights** [View All](#)

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = PIDG
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Receptacle Style <sup>?</sup>	Straight
Barrel Type <sup>?</sup>	Closed Barrel
Wire/Cable Type <sup>?</sup>	Regular Wire
Insulation <sup>?</sup>	Yes
Insulation Support <sup>?</sup>	Insulation Support
Stud Size	8
Shape <sup>?</sup>	RING-043
Heavy Duty <sup>?</sup>	No
Finish <sup>?</sup>	Tin
Color	Red
Electrical Characteristics	
Voltage (VAC)	300
Dimensions	
Insulation Diameter (mm [in]) <sup>?</sup>	2.67 - 3.56 [.105 - .140]
Stud Diameter (mm [in]) <sup>?</sup>	4.34 [0.171]
Tongue Material Thickness (mm [in])	0.79 [0.031]

Body Features	
Body Style <sup>?</sup>	PIDG
Wire Range (mm [AWG]) <sup>?</sup>	0.26-1.04 <sup>2</sup> [22-18]
Material <sup>?</sup>	Copper
Insulation Material	Vinyl
Contact Features	
Terminal Shape <sup>?</sup>	Ring Tongue
Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance <sup>?</sup>	RoHS compliant, ELV compliant
Lead Free Solder Processes <sup>?</sup>	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
Packaging Features	
Packaging Method <sup>?</sup>	Loose Piece
Packaging Quantity	10,000
Other	
Brand	AMP

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Downloaded from [Arrow.com](#)