

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0731160054

Status:

Active

Overview:

RF Connectors and Microwave Products

Description:


MCRF-to-Pigtail, 1.37mm Cable Diameter, Length 76.2mm, H25, 50 Ohms, OnePiece Per Bag

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	73116
Assembly Configuration	Single Ended Connector
Connector to Connector	MCRF-to-Pigtail
Overview	RF Connectors and Microwave Products
Product Name	MCRF, RF
Taxonomy	RF Cable Assemblies
Type	RF Cable Assembly
UPC	884982813571
Physical	
Cable Length	76.20mm (3.000")
Circuits (Loaded)	0
Gender	Plug-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Polyester
Net Weight	0.750/g
Number of Rows	1
Packaging Type	Bag
Single Ended	Yes
Wire/Cable Type	Coaxial
Electrical	
Impedance	50Ω
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-73116-005-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73116 Series

Mates With

734120110 MCRF, 50 Ohm, Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION