

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Latching with side elements, latching with foot element, Basic profile, profile length (configurable): 3 cm ... 200 cm, depth: 19.8 mm, Note: required profile length = PCB length - 16.2 mm



Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2200148/UM122/6.78/GY7035
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	101
Product key	ACHDAA
Customs tariff number	39169010
Country of origin	DE

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing series	UM-PRO
Product family	UM-PRO
Ventilation openings present	no

Dimensions

Depth	19.8 mm
-------	---------

PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

Material specifications

Color (Housing)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

Ambient conditions

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

PCB data

Number of PCB holders	3
Type of PCB mount	Insertion/securing with additional elements
PCB surface	700 mm² ... 1200 mm² (per cm profile length)
Thickness of the PCB	1.4 mm ... 1.8 mm

Mounting

Mounting type	Latching with side elements, latching with foot element
Mounting position	parallel to the DIN rail

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>



UL Recognized
Approval ID: E240868

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035
<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

Mandatory accessories

UM-PRO 72 COVER-L BK - Lateral element

2200151

<https://www.phoenixcontact.com/za/products/2200151>

Lateral element (left) with mounting foot for DIN rails for UM-PRO profiles with a PCB width of 72 mm



UM-PRO 72 COVER-R BK - Lateral element

2200152

<https://www.phoenixcontact.com/za/products/2200152>

Lateral element (right) with mounting foot for DIN rails for profiles for PCB width 72 mm



UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO 108 COVER-L BK - Lateral element

2200155

<https://www.phoenixcontact.com/za/products/2200155>

Lateral element (left) with mounting foot for DIN rails for UM-PRO profiles with a PCB width of 108 mm



UM-PRO 108 COVER-R BK - Lateral element

2200156

<https://www.phoenixcontact.com/za/products/2200156>

Lateral element (right) with mounting foot for DIN rails UM-PRO profiles for PCB width of 108 mm



UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO 122 COVER-L BK - Lateral element

2200158

<https://www.phoenixcontact.com/za/products/2200158>

Lateral element (left) with mounting foot for DIN rails for UM-PRO profiles with a PCB width of 122 mm



UM-PRO 122 COVER-R BK - Lateral element

2200159

<https://www.phoenixcontact.com/za/products/2200159>

Lateral element (right) with mounting foot for DIN rails for UM-PRO profiles for PCB the width of 108 mm



Accessories

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

SZF 0-0,4X2,5 - Screwdriver

1204504

<https://www.phoenixcontact.com/za/products/1204504>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

UM-PRO PE CONTACT L1 - Functional ground contact

2200161

<https://www.phoenixcontact.com/za/products/2200161>



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 1

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO PE CONTACT L2 - Functional ground contact

2200162

<https://www.phoenixcontact.com/za/products/2200162>



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 2

UM-PRO PE CONTACT L3 - Functional ground contact

2200163

<https://www.phoenixcontact.com/za/products/2200163>



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 3

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO PCB S-LOCK BK - Locking

2200168

<https://www.phoenixcontact.com/za/products/2200168>



Locking element for locking the top PCB onto UM-PRO housing close to the edge

UM-PRO PCB C-LOCK L1 BK - Locking

2200164

<https://www.phoenixcontact.com/za/products/2200164>



Locking element for locking the PCB onto UM-PRO housing at level 1

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjJwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO PCB C-LOCK L2 BK - Locking

2200165

<https://www.phoenixcontact.com/za/products/2200165>



Locking element for locking the PCB onto UM-PRO housing at level 2

UM-PRO PCB C-LOCK L3 BK - Locking

2200166

<https://www.phoenixcontact.com/za/products/2200166>



Locking element for locking the PCB onto UM-PRO housing at level 3

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO MOUNT BK - Mounting flange

2200171

<https://www.phoenixcontact.com/za/products/2200171>

Foot element for mounting UM-PRO DIN rail-mount bases directly onto the mounting panel



UM-PRO 72 FOOT BK - Foot element

2200153

<https://www.phoenixcontact.com/za/products/2200153>

Press-drawn section housings, DIN rail mounting, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 72 mm), Foot element



UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO 108 FOOT BK - Foot element

2200157

<https://www.phoenixcontact.com/za/products/2200157>

Press-drawn section housings, DIN rail mounting, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 108 mm), Foot element



UM-PRO 122 FOOT BK - Foot element

2200160

<https://www.phoenixcontact.com/za/products/2200160>

Press-drawn section housings, DIN rail mounting, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 122 mm), Foot element, width: 14.3 mm, height: 135.9 mm, depth: 20.95 mm



UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO A/U N 73 CM - Covering hood

2200310

<https://www.phoenixcontact.com/za/products/2200310>



Press-drawn section housings, Latching, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 24 mm, Note: max. length of the cover = PCB length - 19 mm

UM-PRO A/U 73 CM - Covering hood

2200311

<https://www.phoenixcontact.com/za/products/2200311>



Press-drawn section housings, Latching, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 63.2 mm, Note: max. length of the cover = PCB length - 19 mm

UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO A/U 92 CM - Covering hood

2200312

<https://www.phoenixcontact.com/za/products/2200312>

Press-drawn section housings, Latching, Cover, width: 92 mm, profile length (configurable): 3 cm ... 100 cm, height: 34 mm, Note: max. length of the cover = PCB length - 19 mm



UM-PRO LID-73N BK - Lateral element

2200174

<https://www.phoenixcontact.com/za/products/2200174>

Press-drawn section housings, Latching, Side element for low U-shaped profile cover, width: 10.35 mm, height: 78.43 mm, depth: 29.75 mm



UM-PRO PROFILE - Profile



2200148/UM122/6.78/GY7035

<https://www.phoenixcontact.com/za/products/2200148?orderkey=MjIwMDE0OC9VTTEyMi82Ljc4L0dZNzAzNQ>

UM-PRO LID-73 BK - Lateral element

2200173

<https://www.phoenixcontact.com/za/products/2200173>



Press-drawn section housings, Latching, Side element for U-shaped profile cover, width: 10.35 mm, height: 78.49 mm, depth: 68.95 mm

UM-PRO LID-92 BK - Lateral element

2200172

<https://www.phoenixcontact.com/za/products/2200172>



Press-drawn section housings, Latching, Side element for U-shaped profile cover, width: 10.35 mm, height: 97.51 mm, depth: 39.7 mm

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (Pty) Ltd.
36 Lyn Road P.O. Box 916 ZA-Ferndale 2160

+27/11/801-8200
info@phoenixcontact.co.za