Part Number : 936011019
Product Description : Heavy-Duty Standard (STD) Single Lever Hood, Polyamide, with 2 Pegs, Side Entry, without Cable Gland, Size «32x13», Pg16 Thread, Black
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7808.6640.1



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

Downloaded from Arrow.com.

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Single Lever Hood, Polyamide, with 2 Pegs, Side Entry, without Cable Gland, Size «32x13», Pg16 Thread, Black
Component Type	Single Lever Hood
IP Rating	IP66, IP67
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191865867

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V

Physical

Cable Diameter	8.00-14.00mm
Component Size	«32X13»
Entry Location	Side
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Polyamide
Material - Peg	Polyamide
Net Weight	24.000/g

Downloaded from Arrow.com.

Number of Pegs	2
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts and 8.00-14.00mm Cable Diameter (Pg16) Polyamide Cable Gland

Downloaded from Arrow.com.