**Part Number :** 2167000309
**Product Description :** SlimStack Board-to-Board Receptacle, 0.35mm Pitch, ACB6+ Series, 0.60mm Mated Height, 1.90mm Mated Width, 30 Circuits, 8 Reels/Carton
**Series Number :** 216700
**Status :** Active
**Product Category :** Board-to-Board Connectors



## Documents and Resources

### Drawings

2167000309_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

2167000309.dxf

### Specifications

2167000000-AS-000.pdf

2167000000-SPK-000.pdf

2167000000-SPK-020.pdf

2167000000-PS-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Board-to-Board Connectors |
| Series | 0.35, ACB6+ |
| Description | SlimStack Board-to-Board Receptacle, 0.35mm Pitch, ACB6+ Series, 0.60mm Mated Height, 1.90mm Mated Width, 30 Circuits, 8 Reels/Carton |
| Application | Board-to-Board |
| Component Type | Receptacle |
| Product Name | SlimStack |
| UPC | 195842747746 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 0.3A, 5.0A |
| Voltage - Maximum | 60V AC (RMS)/DC |

### Physical

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 30 |
| Circuits (maximum) | 30 |
| Color - Resin | Black |

Downloaded from Arrow.com.

| | |
|---|---|
| Durability (mating cycles max) | 30 |
| Glow-Wire Capable | No |
| Mated Height | 0.60mm |
| Mated Width | 1.90mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 13.930/mg |
| Number of Rows | 2 |
| Orientation | Vertical |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Retention | Yes |
| Pitch - Mating Interface | 0.35mm |
| Pitch - Termination Interface | 0.35mm |
| Plating min - Mating | 0.100µm |
| Plating min - Termination | 0.050µm |
| Polarized to Mating Part | No |
| Polarized to PCB | No |
| Temperature Range - Operating | -40° to +85°C |
| Termination Interface Style | Surface Mount |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| SlimStack Board-to-Board Plug, 0.35mm Pitch, ACB6+ Series, 0.60mm Mated Height, 1.90mm Mated Width, 30 Circuits, 8 Reels/ Carton | 2167010309 |



Downloaded from Arrow.com.