
**Part Number :** 2181011040
**Product Description :** Micro-Lock Plus-to-Micro-Lock Plus Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 50.00mm Length, 4 Circuits, Black
**Series Number :** 218101
**Status :** Active
**Product Category :** Power and Signal Cable Assemblies



## Documents and Resources

### Drawings

2181011040_sd.pdf

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 218101 |
| Description | Micro-Lock Plus-to-Micro-Lock Plus Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 50.00mm Length, 4 Circuits, Black |
| Application | Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Micro-Lock Plus-to-Micro-Lock Plus |
| Keyword | Micro-Lock Plus 2.0 |
| Product Name | Micro-Lock Plus |
| Type | Discrete Wire Assembly |
| UPC | 195842350205 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 250V AC (RMS)/DC |

### Physical

| | |
|---|---|
| Cable Length | 50.00mm |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |

Downloaded from Arrow.com.

| | |
|---|---|
| Color - Resin | Black |
| Gender | Female-Female |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Polyester |
| Net Weight | 1.822/g |
| Number of Rows | 1 |
| Overmolded | No |
| Packaging Type | Bag |
| Pitch - Mating Interface | 2.00mm |
| Plating min - Mating | 0.700µm |
| Single Ended | No |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 10002 |
| Wire Size (AWG) | 22 |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| 2.00mm Pitch Micro-Lock Plus Vertical, Single Row, Surface Mount Headers | 505575 |
| 2.00mm Pitch Micro-Lock Plus Right-Angle, Single Row, Surface Mount Headers | 505578 |
| 2.00mm Pitch, Micro-Lock Plus Single Row Plug Housings | 213719 |



Downloaded from Arrow.com.