



Part Number : [1054390005](#)
Product Description : Anti-Snag Spring Clip,
1.32mm Width, 0.25µm Gold (Au) Plating,
1.40mm -2.00mm Working Range (Height)
Series Number : 105439
Status : Active
Product Category : Connector Accessories



Documents & Resources


Drawings
[1054390005_sd.pdf](#)
[PK-105439-001-001.pdf](#)

3D Models and Design Files
[1054390005_stp.zip](#)

Specifications
[PS-105439-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Accessories
Series	105439
Description	Anti-Snag Spring Clip, 1.32mm Width, 0.25µm Gold (Au) Plating, 1.40mm -2.00mm Working Range (Height)
Component Type	Clip
Product Name	Spring Clip
UPC	889056318648

Electrical

Current - Maximum per Contact	1.5A
-------------------------------	------

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Material - Metal	Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.008/g
Packaging Type	Embossed Tape on Reel
Plating min - Mating	0.254µm
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Solder