

Han 16B HTE M32 PFT CL



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 016 1141
Specification	Han 16B HTE M32 PFT CL
HARTING eCatalogue	https://b2b.harting.com/19300161141

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Panel feed through housing
Type	High construction

Version

Locking type	Central locking lever (on the hood)
Size	16 B
Version	Top entry
Cable entry	1x M32
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

CE	Yes
----	-----

Commercial data

Packaging size	1
Net weight	352.7 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors