

**Product Name // Flex Cable Connector PXM6010 Series 4**  
**Contact Socket Crimp/Solder Termination (contacts available separately) 7mm-9mm Cable (Yellow Gland) Metal Body No Braid Termination**


[View Product Page](#)


Image not found or type unknown

### // Product Description:

- ⬢ Flex Cable Connectors
- ⬢ Water and dustproof to IP66, IP68, IP69K when mated with compatible connector
- ⬢ 30 degree push twist locking, tamperproof lock prevents accidental un-mating
- ⬢ Socket
- ⬢ 4 Contacts
- ⬢ Crimp/solder termination with contacts and fitting tool available separately
- ⬢ Metal Body No Braid Termination
- ⬢ Cable acceptance 7mm-9mm diameter
- ⬢ Gland Pack PXP6088 available separately to accommodate all sizes
- ⬢ PXM6081 Sealing Cap available separately to maintain IP rating of unmated connectors
- ⬢ Mate with PXM6011 Series Inline and PXM6012 Series Front Panel Mount Connectors

### // General Information:

Product Display Title:	Flex Cable Connectors
Product Family:	Circular Power Connectors
Product Series:	6000 Series Buccaneer
Body Colour:	Metallic Grey
Body Material:	Brass
Body Material Type:	Metal Body No Braid Termination
Contact Type:	Socket Contact
Coupling Type:	Push-Twist
Current Max:	10A, 4A, 7A
Diameter Over Coupling Ring Mm:	32mm
Function:	Flex Cable Connector
Insulation Resistance:	>10 <sup>6</sup> MΩ @500V DC
Ip Rating:	IP66, IP68, IP69K
Max Cable Entry Size:	9mm
Min Cable Entry Size:	7mm
Max Contact Accommodation Awg:	18AWG
Min Contact Accommodation Awg:	20AWG
Max Contact Accommodation Mm2:	0.75mm <sup>2</sup>
Min Contact Accommodation Mm2:	0.5mm <sup>2</sup>
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	4 Contacts
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	EN60068-2-11 Test Ka Salt Mist
Voltage Max:	277V

#### // Product PDF Links

[6000 Series power connectors...](#)
[6000 Series metal body power...](#)

#### // Product 3D CAD Model Links

[PXM6010/04S/CR/07093D CAD Model](#)