



Quick Links

[Cross reference](#)
[RoHS/LF P/N Search](#)
[Industry Standards](#)
[Alphabetical List](#)

Documentation

[3D model search](#)
[Customer drawing search](#)
[Free search](#)
[Search by category](#)

Services

[E-Services](#)
[Distributor list](#)

Start> Search="10102782-001LF" > 10102782-001LF

10102782-001LF

10102782-001LF : MMI 20P PLUG



Customer drawing



Environmental Compliance Report

ACTIVE

[Add to Favorites](#)

[Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)
 [Sample request](#)

[Specifications](#) [Download document](#)

[General](#) [Electrical](#) [Physical](#) [Other Features](#)

General	
Number of contacts	20
Product Type	Plug
Electrical	
Current rating	1A
Resistance (Contact)	Before: 50m ohms max After: 100m ohms max
Resistance (Insulation)	1000 M-ohms min
Physical	
Color (Housing)	Black
Material (Contact)	Copper Alloy
Material (Housing)	Thermoplastic
Plating (Contact)	Ni:1.27 to 3.0 um (Au: Min 0.2 um)
Temperature (Operating - range)	-40°C to +85°C
Other Features	
Packaging (Type)	Tray