

Product data sheet

Specifications



APC IT Power Distribution Module 3 Pole 5 Wire 63A IEC309 440cm

PDM3563IEC-440

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Colour	Grey
Depth	30.5 cm
Height	15.2 cm
Net weight	15.91 kg
Width	26.7 cm

Input

Max line current	63 A
Input voltage	400 V 3 phases

Output

Max current draw	63 A
Number of power socket outlets	1 IEC 309
Output voltage	230 V 400 V 3 phases

Conformance

Product certifications	CE VDE
------------------------	-----------

Environmental

Ambient air temperature for operation	0...30 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft

Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...4572.00 m

Packing Units

Package 1 Weight	17.73 kg
Package 1 Height	22.9 cm
Package 1 width	50.8 cm
Package 1 Length	50.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------