

**Part Number :** 1300642019
**Product Description :** BradPower D-Size (1 3/8"–M35) Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 10 AWG, Black TPE Cable, Red Overmold, 8.0m (26.25') Length
**Series Number :** 130064
**Status :** Active
**Product Category :** Industrial Cable Assemblies
**Engineering Part Number :** CC3030K19M080E

## Documents and Resources

### Drawings

1300642019_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Compliant with Exemption 3 per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Contains Lead per D(2022)9120-DC (17 Jan 2023) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Industrial Cable Assemblies |
| Series | 130064 |
| Description | BradPower D-Size (1 3/8”–M35) Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 10 AWG, Black TPE Cable, Red Overmold, 8.0m (26.25') Length |
| IP Rating | IP67 |
| Product Name | BradPower D-Size |
| Type | Double Ended |
| UPC | 78172552062 |

### Agency

| | |
|---|---|
| UL | E258922 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 32.0A |
| Voltage - Maximum | 600V AC/DC |

### Physical

| | |
|---|---|
| Cable Diameter | 11.48mm (.452") |
| Cable Length | 8.0m (26.25') |
| Color - Cable Jacket | Black |
| Connector End A | BradPower D-Size (1 3/8”–M35) |
| Connector End B | BradPower D-Size (1 3/8”–M35) |
| Coupling Style | Threaded |

Downloaded from Arrow.com.

| | |
|---|---|
| Gender | Female-Male |
| Keyway | Single |
| LED Indicator | None |
| Material - Cable Jacket | TPE |
| Material - Connector Body | TPE |
| Material - Contact | Copper Alloy |
| Material - Coupling Nut | Anodized Aluminum |
| Material - Plating Mating | Gold |
| Net Weight | 886.000/g |
| Orientation | Straight to Straight |
| Poles | 3 |
| Temperature Range - Operating | -20° to +90°C |
| Wire/Cable Type | TC-ER |
| Wire Size (AWG) | 10 |



Downloaded from Arrow.com.