







注) 1. 材 質
NOTES MATERIAL
モールドカバー⁹⁹ A⁹⁹ : ガラス入りポリカーボネイト樹脂
MOLD COVER "A" : POLYCARBONATE G.F.
UL 94V-0 色 : SEE TABLE
UL94V-0 COLOR : SEE TABLE
スプリングラッチ : ステンレス鋼 t0.4
SPRING LATCH : STAINLESS STEEL t0.4
2. 適用プラグカバーB : 54182-060*
APPLICABLE PLUG COVER B : 54182-060*





BLACK	54181-0616	54181-061*
GRAY	54181-0615	
COLOR	MATERIAL No.	MODEL No.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		4:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 627599 DRWN: KTAKEUCHI01 2019/10/02 CHK'D: TKON 2019/11/19 APPR: ASHIMOTSU 2019/11/19											
ANGULAR TOL ± 1.0 °															
4 PLACES		± 0.2													
3 PLACES		± 0.2													
2 PLACES		± 0.2		INITIAL REVISION: DRWN: RFC_PLMIMP 2017/12/25 APPR: RFC_PLMIMP 2017/12/25				PRODUCT CUSTOMER DRAWING							
1 PLACE		± 0.2						DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
0 PLACES		± 0.2						SD-54181-0615		PSD		001		B	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		54181		SEE TABLE		GENERAL MARKET		1 OF 1	


部品構成
PARTS CONSTRUCTION

部番 NO.	部品名 PART NAME	製品番号 ENG. NO.	個数 QUAN.	材質 MATERIAL
①	ハウジングアッセンブリ HOUSING ASS'Y	54180-0619	1	ハウジング：ガラス入り耐熱樹脂 UL94V-0 色：黒 HOUSING：G.F. HEAT RESISTANT PLASTIC UL94V-0 COLOR：BLACK ターミナル：りん青銅 t0.3 TERMINAL：PHOSPHOR BRONZE t0.3 メッキ仕様 接点部：ニッケル下地金メッキ PLATING CONTACT AREA：GOLD OVER NICKEL 結線部：ニッケル下地錫メッキ WIRE TERMINATION AREA：TIN OVER NICKEL
②	カバーA COVER A	54181-0615	1	カバーA：ガラス入りポリカーボネイト樹脂 COVER A：POLYCARBONATE G.F. UL94V-0 色：グレー UL94V-0 COLOR：GRAY スプリングラッチ：ステンレス鋼 t0.4 SPRING LATCH：STAINLESS STEEL t0.4
③	カバーB COVER B	54182-0605	1	ガラス入りポリカーボネイト樹脂 UL94V-0 色：グレー POLYCARBONATE G.F. UL94V-0 COLOR：GRAY
④	シエル カバー SHELL COVER	58299-0626	1	鋼 t0.4 STEEL t0.4
⑤	シエル ボディ SHELL BODY	58300-0626	1	メッキ仕様：ニッケル下地、錫メッキ PLATING：NICKEL BASE，TIN PLATING
⑥	ケーブルクランプ CABLE CLAMP	58303-0000	1	ステンレス鋼 STAINLESS STEEL
⑦	十字穴付きなべ小ネジ CROSS RECESSED PAN HEAD MACHINE SCREW	59832-0009	2	黄銅(ネジサイズ：M2X4) BRASS (SCREW SIZE：M2X4)


NOTES:
本製品は55100-0600の鉛フリー品である
THIS PRODUCT IS LEAD FREE OF 55100-0600.





HOUSING ASS'Y



CABLE CLAMP



SCREW



SHELL BODY

GRAY	TRAY & POLY BAG	55100-0680	55100-***0
	POLY BAG	55100-0670	
COVER COLOR	PACKAGE METHOD	MATERIAL No.	MODEL No.







THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex									
mm		NTS															
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 627599 DRWN: KTAKEUCHI01 2019/10/02 CHK'D: TKON 2019/11/19 APPR: ASHIMOTSU 2019/11/19				2.0 I/O CONN.PLUG SET									
ANGULAR TOL ± °																	
4 PLACES		±															
3 PLACES		±															
2 PLACES		±															
1 PLACE		±		INITIAL REVISION: DRWN: HKAWABATA 2004/05/21 APPR: MSASAO 2004/05/21				PRODUCT CUSTOMER DRAWING									
0 PLACES		±															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
						A3-SIZE		55100		SD-55100-004		PSD		001		C	
										MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
										SEE TABLE		GENERAL MARKET				1 OF 2	

DOCUMENT STATUS	P1	RELEASE DATE	2019/11/19	08:11:00
-----------------	----	--------------	------------	----------


部品構成
PARTS CONSTRUCTION

部番 NO.	部品名 PART NAME	製品番号 ENG. NO.	個数 QUAN.	材質 MATERIAL
①	ハウジングアッセンブリ HOUSING ASS'Y	54180-0619	1	ハウジング：ガラス入り耐熱樹脂 UL94V-0 色：黒 HOUSING：G.F. HEAT RESISTANT PLASTIC UL94V-0 COLOR：BLACK ターミナル：りん青銅 t0.3 TERMINAL：PHOSPHOR BRONZE t0.3 メッキ仕様 接点部：ニッケル下地金メッキ PLATING CONTACT AREA：GOLD OVER NICKEL 結線部：ニッケル下地錫メッキ WIRE TERMINATION AREA：TIN OVER NICKEL
②	カバーA COVER A	54181-0616	1	カバーA：ガラス入りポリカーボネイト樹脂 COVER A：POLYCARBONATE G.F. UL94V-0 色：黒 UL94V-0 COLOR：BLACK スプリングラッチ：ステンレス鋼 t0.4 SPRING LATCH：STAINLESS STEEL t0.4
③	カバーB COVER B	54182-0606	1	ガラス入りポリカーボネイト樹脂 UL94V-0 色：黒 POLYCARBONATE G.F. UL94V-0 COLOR：BLACK
④	シエル カバー SHELL COVER	58299-0626	1	鋼 t0.4 STEEL t0.4
⑤	シエル ボディ SHELL BODY	58300-0626	1	メッキ仕様：ニッケル下地、錫メッキ PLATING：NICKEL BASE，TIN PLATING
⑥	ケーブルクランプ CABLE CLAMP	58303-0000	1	ステンレス鋼 STAINLESS STEEL
⑦	十字穴付きなべ小ネジ CROSS RECESSED PAN HEAD MACHINE SCREW	59832-0009	2	黄銅(ネジサイズ：M2X4) BRASS (SCREW SIZE：M2X4)

NOTES:
本製品は55100-0600の鉛フリー品である
THIS PRODUCT IS LEAD FREE OF 55100-0600.



BLACK	POLY BAG	55100-0671	55100-***1
COVER COLOR	PACKAGE METHOD	MATERIAL No.	MODEL No.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex										
mm		NTS															
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 627599 DRWN: KTAKEUCHI01 2019/10/02 CHK'D: TKON 2019/11/19 APPR: ASHIMOTSU 2019/11/19			2.0 I/O CONN.PLUG SET										
ANGULAR TOL ± °																	
4 PLACES		±															
3 PLACES		±															
2 PLACES		±															
1 PLACE				INITIAL REVISION: DRWN: HKAWABATA 2004/05/21 APPR: MSASAO 2004/05/21			PRODUCT CUSTOMER DRAWING										
0 PLACES																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
						A3-SIZE		55100		SD-55100-004		PSD		001		C	
										MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
										SEE TABLE		GENERAL MARKET				2 OF 2	

DOCUMENT STATUS	P1	RELEASE DATE	2019/11/19	08:11:00
-----------------	----	--------------	------------	----------