



Part Number : [1300000047](#)
Product Description : Quick-Change Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 0.91m (3.0') Length
Series Number : 130000
Status : Obsolete
Product Category : Circular Industrial Cordsets
Engineering Number : 32353



Documents & Resources

Product Environment Compliance

Compliance

| | |
|--------------------|--------------------|
| GADSL/IMDS | Product not active |
| China RoHS | Product not active |
| EU ELV | Product not active |
| Low-Halogen Status | Product not active |
| REACH SVHC | Product not active |
| EU RoHS | Product not active |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Obsolete |
| Category | Circular Industrial Cordsets |
| Series | 130000 |
| Description | Quick-Change Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 0.91m (3.0') Length |
| IP Rating | IP67 |
| Product Name | Quick-Change |
| Type | Single Ended |
| UPC | 78678832353 |

Agency

| | |
|-----|--------|
| CSA | LR6837 |
| UL | E46237 |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 25.0A |
| Voltage - Maximum | 600V |

Physical

| | |
|---------------------------|-----------------|
| Cable Diameter | 16.63mm (.655") |
| Cable Length | 0.91m (3.0') |
| Color - Cable Jacket | Yellow |
| Connector End A | Quick-Change |
| Connector End B | Pigtail |
| Coupling Style | Threaded |
| Gender | Male-Pigtail |
| Keyway | Single |
| LED Indicator | None |
| Material - Cable Jacket | CPE |
| Material - Connector Body | TPE |
| Material - Contact | Copper Alloy |

| | |
|-------------------------------|---------------------|
| Material - Coupling Nut | Nylon |
| Material - Plating Mating | N/A |
| Net Weight | 455.000/g |
| Orientation | Straight to Pigtail |
| Poles | 3 |
| Temperature Range - Operating | -20° to +105°C |
| Wire/Cable Type | SOW |
| Wire Size (AWG) | 12 |

This document was generated on Sep 24, 2025

Obsolete