



+ CABLE ASSEMBLIES

PLUGGABLE I/O CABLE ASSEMBLIES



☒ Preliminary

TE CONNECTIVITY (TE)
MICROQSFP TO MICROQSFP, 1M 32AWG

microQSFP

|
microQSFP

2821236-2
TE Internal Number: 2821236-2

- EU RoHS Compliant
- EU ELV Compliant
- Cable Assembly Type Pluggable / Direct Attach
- Wire Size (AWG) 32
- Cable Assembly Length (m) 1
- Color Black
- Flammability Rating VW-1

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

CABLE ASSEMBLY MICRO QSFP TO MICRO QSFP 32 AWG
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

EEPROM Map EDR Straight Assembly

PDF

English

MicroQSFP Brochure

PDF

English

MicroQSFP Cable Assembly Technical Datasheet

PDF

English

EEPROM Map MicroQSFP Straight Assembly

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Cable Assembly Type** Pluggable / Direct Attach
- Connector Type (End A)** microQSFP
- Connector Type (End B)** microQSFP
- Cable Assembly Category** High Speed
- Product Type** Cable Assembly
- Latching Style** Pull Tab Release

Configuration Features

- Number of Positions** 8-Pair
- Number of Signal Positions** 16
- Configuration** Double-Ended

Electrical Characteristics

- Impedance (Ω)** 100

Signal Characteristics

- Data Rate (Gb/s)** 25

Body Features

Color Black

Dimensions

Wire Size (AWG) 32
Cable Assembly Length (m) 1

Operation/Application

Halogen Free No

Industry Standards

Flammability Rating VW-1

Statement of Compliance

Statement of Compliance
PDF