

Part number

CK 03 I



Bulkhead mounting housing, CK series, with 1 lever, size "21.21", white colour

Product description		Material properties	
Product type	Bulkhead mounting housing	Other materials	Lever: Polyamide (PA) Gasket: TPE
Series	CK	Colour	RAL 7035 grey
Closing type	With 1 lever	RoHs conformity	Compliant
Size	Size "21.21"	China RoHs - EFUP	E
Cable entry	Without cable entry	REACH SVHC substances	No
Specification	White colour	Approvals / Standards	
Technical data		UL	ECBT2
IP degree of protection	IP44 - IP66 / IP67 / IP69 with CKR 65	cUL	ECBT8
Further technical details		General ordering information	
Weight	9,50 g	EAN13 code	8015747026246
Operating temperature range (min, max)	-40°C...+125°C	eCl@ss 8.1	27440202
		ETIM 7.0	EC000437
		Packaging Information	
		Packaging length	230,00 mm
		Packaging height	160,00 mm
		Packaging width	330,00 mm
		Packaging weight	1,73 kg
		Packaging volume	12,14 dm ³
		Packaging description	Carton box
		Packaging quantity	100 Pcs
		Packaging EAN code	8015747026253
		Sub-packaging weight	0,17 kg
		Sub-packaging description	Carton box
		Sub-packaging quantity	10 Pcs
		Sub-packaging EAN barcode	8015747026260

Part number



CK 03 I

Catalogue drawings



Catalogue drawings



Notes

Dimensions shown in mm are not binding and may be changed without notice.
