




Part Number : [1300360010](#)
Product Description : Mini-Change DeviceNet
Passive 8 Junction
Series Number : 130036
Status : Active
Product Category : Passive Distribution Boxes
Engineering Number : DN8000



Documents & Resources

Drawings

[1300360010_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	130036
Description	Mini-Change DeviceNet Passive 8 Junction
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	DeviceNet,Mini-Change
UPC	78678801263

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	7.0A
Functional Wiring	Parallel
Voltage - Maximum	120V AC/DC
Wiring Configuration	Passive Drop

Physical

Bus I/O	Mini-Change
Cable Connector Orientation	N/A
Cable Length	N/A
Home Run Cable Length	N/A
Home Run Connector	N/A
Home Run Interface	N/A
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC

Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	732.551/g
Orientation	Side Mount
Poles	5
Poles (wired)	5
Ports	8
Temperature Range - Operating	0°C to +60°C

This document was generated on Sep 24, 2025