

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0797582067](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead High-Power MultiCat Female-to-MultiCat Female, Gold (Au) over Nickel Phosphorus (NiP) Plating, 150.00mm Length, 12 AWG, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">79758</a>
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	MultiCat Crimp Terminals
Overview	<a href="#">Off-the-Shelf Pre-Crimped Leads</a>
Product Name	MultiCat
UPC	191128292757

**Physical**

Cable Length	150.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel Phosphorus
Material - Plating Termination	Gold
Net Weight	8.565/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.30mm
Wire Size AWG	12
Wire/Cable Type	UL 1199

**Electrical**

Current - Maximum per Contact	26.0A
-------------------------------	-------

**Material Info**

Engineering Number	F30H1288L150
--------------------	--------------

**Reference - Drawing Numbers**

Sales Drawing	797582065-000
---------------	---------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[79758 Series](#)

**Use With**

MultiCat High-Power Circular Receptacle Housing [200915](#) . MultiCat High-Power Inline Receptacle Housing [201841](#)