


4

3

2

1

UNIT:mm



5000±50

5.5±0.2

12.0±0.3

P1

P2


PIN ASSIGNMENT

P1 RED 1
P2 WHITE 1
P3 GREEN 2
P4 BLACK 3
P5 DRAIN+BRAID 4
P6 SHELL 4

Electrical test:

- 1. 100% short, open, miswire test
- 2. Conduct resistance: 5 Ohm(max)
- 3. Insulation resistance: 10Mohm(min)
- 4. dielectric test: DC 300V

1PC/PE BAG



⑧	TIE	1	BLACK L=100mm
---	-----	---	---------------

⑦	PE BAG	1/5	CLEAR SIZE: 330*380*0.05mm PRINT BLACK"MADE IN CHINA"+"5PCS"及印生产周期,有透气孔.
---	--------	-----	--

⑥	PE BAG	1	CLEAR SIZE: 210*250*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"及印生产周期,有透气孔.
---	--------	---	---

⑤	OUT JACKET	6g	BLACK PVC-40P (MOULD NO:WM-40)
---	------------	----	--------------------------------

④	OUT JACKET	6g	BLACK PVC-40P (MOULD NO:WM-173)
---	------------	----	---------------------------------

③	CABLE	1	USB2.0 UL2725 [28AWG(7/0.12TC+AL)*1P+28AWG(7/0.12TC)*2C]+AEB(48B TC)
---	-------	---	--

②	CONN	1set	USB A MALE SHELL:NICKEL PIN:G/F 3PCS TYPE INSULATOR COLOR:WHITE
---	------	------	---

①	CONN	1	MICRO USB 5P A/M SOLDER TYPE SHELL:NICKEL PIN:G/F INSULATOR COLOR:BLACK
---	------	---	---

NO.	NAME	Q'TY	SPECIFICATION
-----	------	------	---------------

4

3

2

1

CNC Tech, LLC
Industrial Cable and Connector Technology

DRAWN ZHONGHS DRAWING NO

CHECKED CUSTOMER

APPROVAL ITEM NO. 102-1072-BL-00500

DECIDED DATE 2012-02-16

VERSIONS/EDITION A/0 PROJECTION

A

B

C

D