Specifications



Photo is representative





Eaton HCP0704-R60-R

Eaton HCP0704 inductor, 0.6 uH, 14 A Irms, 21 A ISAT, 5 mΩ resistance, SMT mounting, Iron Powder, 2-pins, 1000 qty.

General specifications	
PRODUCT NAME	Eaton HCP0704 inductor
CATALOG NUMBER	HCP0704-R60-R
UPC	051712544085
PRODUCT LENGTH/DEPTH	6.8 mm
PRODUCT HEIGHT	4.2 mm
PRODUCT WIDTH	6.8 mm
PRODUCT WEIGHT	0.99 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	14 A
ISAT	21 A
PACKAGE QUANTITY	1000
MATERIAL	Iron powder
FREQUENCY RATING	Up to 2 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 155 °C
RESISTANCE	5 mΩ
SERIES	HCP0704

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - HCP0704-R60-R Eaton HCP0704 high current power inductors data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.