

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130102-0083](#)
Status: **Active**
Description: Super-Safeway™ Rubber Hand Lamp Only with 100W Quick Open Guard and Reflector with Switch

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA	LR85374
UL	E59251

General

Product Family	Portable Lighting
Series	130102
NEMA Configuration	N/A
Outlet	None
Product Literature Order No	987650-8053
Product Name	Super-Safeway™
Type	Hand Lamps
UPC	78678860361
Woodhead	Yes

Physical

Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	No
Guard Type	Metal Wire
Height	374.65mm (14.750")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

Material Info

Old Part Number	105S
-----------------	------



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130102Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION