



Part Number : [1300980425](#)
Product Description : MAX-LOC Strain Relief Cord-
Sealing Grip, 3/8" NPT, 90° Angle Male, Cable
Diameter 6.35-7.93mm (.250-.312")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Number : 5505



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/8" NPT, 90° Angle Male, Cable Diameter 6.35-7.93mm (.250-.312")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78172538322

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	6.35-7.93mm (.250-.312")
Color - Grommet	Black
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
O-Ring	No
Thread Size	3/8" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/8" NPT	<u>1300990142</u>
MAX-LOC Gasket Sealing Ring, 3/8" NPT, Black	<u>1300990148</u>

This document was generated on Sep 22, 2025