

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)
- M12 (B)
- M12 (D)
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (X)
- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



M12A-03BFFM-SL8D01

- Operating Temperature: -20°C ~ +80°C
- Transmission Speed: N/A
- Shielded: Metal, Non-shielded
- Jacket Material: PVC
- Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity

- 1 +

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

M Series....
CAP-WBDF SMA1
-40°C ~ +105°C

- 0 +

M Series....
CAP-WBDF SMA2
-40°C ~ +105°C

- 0 +

M Series....
CAP-WBDF SPB1
-40°C ~ +105°C

- 0 +

M Series....
IA-A03M-A03M-...
-20°C ~ +85°C

- 0 +

M Series, M12, A...
M12A-03BMMA-...
-40°C ~ +105°C

- 0 +

M Series, M12, A...
M12A-03BMMA-...
-40°C ~ +105°C

- 0 +

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 4A	Connector Type Overmolded
Shielded Metal, Non-shielded	No. of Contacts 03
Connector Gender Female	Backshell Straight
Mating Style Screw Thread	IP Rating IP68
Assembly Style N/A	
<div><div></div>More Options</div>	

People Also Bought

M12A-03BFFM-...

AB-CD09FR-COBR-...

SDB25FL-SDBFL-...

BD-06BMFA-QL8MP0

AA-BU12FL-BUFL-...

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

Downloaded from [Arrow.com](#)