
Part Number : WTAX24SACJT
Product Description : AirBorn W Series Rectangular Board Mount Receptacle with Socket Contacts, Vertical, Solder Cup, Dual Row, 0.100"/2.54mm Pitch, Plastic Body, without Mounting Ears, Turning Jackset (.500"), 24 Circuits
Status : Active
Product Category : I/O Connectors



Documents and Resources

Specifications

Materials Specification

Performance Specification

Face Seal Gaskets (WTA-WTB Series)

Hoods (WTA-WTAX Series)

Solder Cup Adapter Sleeve, Coax Removal Tool, Extension Nuts

Nut Spanner Wrenches, Insertion & Removal Tools, Crimp Tools & Positioners

Contacts (WT, WTA, WTB, WTK, WG, WGA)

Hardware Availability (pg 1)

Hardware Availability (pg 2)

Polarizing Pin Applications

Dimensional Information

Hardware Dimensions (Guide)

Part Number Buildup

Part Details

General

Status	Active
Category	I/O Connectors
Description	AirBorn W Series Rectangular Board Mount Receptacle with Socket Contacts, Vertical, Solder Cup, Dual Row, 0.100"/2.54mm Pitch, Plastic Body, without Mounting Ears, Turning Jackset

Downloaded from Arrow.com.

	(.500"), 24 Circuits
Application	Wire-to-Board
Comments	Socket, Straight, Solder Cup (.035" I.D.)
Component Type	Receptacle
Contact Type	Socket
Product Name	AirBorn W Series

Electrical

Current - Maximum per Contact	5.0A
Data Rate	1.0 Gbps
Voltage - Maximum	1000V

Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Gray
Durability (mating cycles max)	500
Gender	Female
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Locking Type	Turning Jackset, 0.500"
Material - Plating Mating	Gold
Material - Shell	Polyphenylene Sulfide
Mounting Style	Without Mounting Ears
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.100" (2.54mm)
Pitch - Termination Interface	0.100" (2.54mm)
Plating min - Mating	50µ”
Polarized to Mating Part	No
Temperature Range - Operating	-65° to +125°C

Downloaded from Arrow.com.

Termination Interface Style	Solder Cup

Mates With / Use With

Mates with Part(s)

Description
Rectangular, Plastic, 2 Row, Vertical Board or Cable Mount Plug
Rectangular, Plastic, 2 Row, Vertical Board or Cable Mount Plug
Rectangular, Plastic, 2 Row, Right Angle Board or Cable Mount Plug
Rectangular, Plastic, 2 Row, Vertical Board or Cable Mount Plug
Rectangular, Plastic, 2 Row, Crimp Removable Cable Mount Plug
Rectangular, Plastic, 2 Row, Crimp Removable Cable Mount Plug

Downloaded from Arrow.com.