Part Number : 1300480319
Product Description : Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male (Straight), 24 AWG, Teal TPE Cable, 42.0m (137.80') Length
Series Number : 130048
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : E11A06004M420



Documents and Resources

Drawings

1300480319_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130048
Description	Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male (Straight), 24 AWG, Teal TPE Cable, 42.0m (137.80') Length
IP Rating	IP67
Performance Category	5e
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78172547695

Agency

UL	E200650

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Physical

Cable Diameter	6.10mm (.240")
Cable Length	42.0m (137.80')

Downloaded from Arrow.com.

Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	1694.000/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +75°C
Wire/Cable Type	Unshielded TPE/AWM 2463
Wire Size (AWG)	24

Downloaded from Arrow.com.