




EuropacPRO Side Panel, Type F, Flexible, 6 U, 235 mm

CATALOG NUMBER

34560-487



Combinations of horizontal rails and side panels

⊕ = can be combined ⊖ = combination not recommended

	Support 19"	Support 19"	Support 19"	Support 19"
Support 19"	⊖	⊕	⊕	⊕
Support 19"	⊕	⊕	⊕	⊕
Support 19"	⊕	⊕	⊕	⊕
Horizontal rail	⊕	⊕	⊕	⊕
Side panel	⊕	⊕	⊕	⊕

Light 19" Flexible 19" Heavy 19" Support 19"

⊕ = can be combined ⊖ = combination not recommended

Flat Side Panel for separate screw-mountable 19" bracket.

CERTIFICATIONS



FEATURES

Flat side panel for separate screw-mountable 19" bracket

Versions for EMC sealing (stainless steel or textile) side panels type F, 19" bracket, corner profile, EMC sealing, wall mounting, side panel linking, handles, panel fitting

PRODUCT ATTRIBUTES

Rack Height: 6U

Package Quantity: 1

Finish: Passivated

Material: Aluminum

Product Family: EuropacPRO

Product Type: Side Panel

Type: Type F

Works With: Subracks

ADDITIONAL PRODUCT DETAILS

Further components for construction of a shielded or unshielded subrack: 19" bracket, corner profile; Horizontal rails; Guide rails; Cover plates; Rear/front; Handles; EMC shielding; Internal assemblies.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE