







TCPN	TE Product Type (Entretec)	RAL NUMBER	COLOR	Width A	Height B	Depth C
1SNG604005R0000	EP-BPA-SZ10-LGR-A	7035	L.Grey	156.5	75.5	27.2
1SNG604006R0000	EP-BPA-SZ10-BL-A	9005	Black	156.5	75.5	27.2

TE CONNECTIVITY CONICAL GROMMET CABLE PLATES PROPERTIES	
BPA (S)-10 WAYS	
PROPERTY	SPECIFICATION
CABLE CLAMPING SCREWS	IMBUS STEEL / 12 pcs - Ø4x28 mm PUSH DWEL TIGHTEN
WORKING TEMPERATURE	-40°C to +80°C
CLAMPING RANGE	A1 + A2 Seal
CABLE ENTRIES	10 ways
PLATE FIXATION SCREWS	4 pcs - M4x20mm



SEAL DIMENSIONS			
Seal Size	Related Oninon Seal	Central After Peeling	Cable Clamping Range Ø mm
A1	01-Ø4/Ø5	1	3.5 to 5.5
	02-Ø6/Ø7	2	5.5 to 7.5
	03-Ø8/Ø9	3	7.5 to 9.5
A2	01-Ø10/Ø11	1	9.5 to 11.5
	02-Ø12/Ø13	2	11.5 to 13.5
	03-Ø14/Ø15	3	13.5 to 15.5

9	1	ENCLOSURE	-	GENERIC	-
8	4	M4x20 SCREW	-	STEEL (STANDARD)	-
7	4	BLIND PLUG RUBBER	-	THERMOPLASTIC ELASTOMER	-
6	10	SEALING RUBBER	-	THERMOPLASTIC ELASTOMER	-
5	1	FRAME SEALING	-	PU (PLOYURETHANE) OR SILICON	-
4	1	CENTRAL INSERT	-	PA 6 (+GF)	-
3	1	PRESSURE PLATE	-	PA 6 (+GF)	-
2	1	PRESSURE CAP	-	PA 6 (+GF)	-
1	1	MAIN BODY	-	PA 6 (+GF)	-
RPT	QTY	DOC TITLE	DRAWING NUMBER	MATERIAL	COMMENTS
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Rajan, M. Kas	25FEB2022	TE Connectivity	
		CHK Rafeeq, Mohd	25FEB2022		
		APVD Rafeeq, Mohd	25FEB2022		
		PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME BPA-CABLE-PLATE	
		0 PLC ±1		SIZE CAGE CODE DRAWING NO	
		1 PLC ±1		A1 00779	
		2 PLC ±1		©=1SNP061340-0100	
		3 PLC ±1		RESTRICTED TO	
		4 PLC ±1		SCALE 2:1 SHEET 1 OF 1 REV A	
MATERIAL REF. TABLE		-		CUSTOMER DRAWING	
		-			