

M12 Power Male PE Contact Crimp 0,75mm²



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9928
Specification	M12 Power Male PE Contact Crimp 0,75mm²
HARTING eCatalogue	https://b2b.harting.com/21011009928

Identification

Category	Contacts
Series	Circular connectors M12
Identification	Power
Type of contact	Crimp contact
Description of the contact	FE contact 24.8 mm length

Version

Gender	Male
Manufacturing process	Turned contacts
Details	use with M12 Power female contacts

Technical characteristics

Conductor cross-section	0.75 mm²
Conductor cross-section	AWG 20
Performance level	1

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead

Specifications and approvals

PROFINET	Yes
----------	-----

Commercial data

Packaging size	50
Net weight	0.76 g
Country of origin	Switzerland
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors