

**Part Number :** [1301500059](#)

**Product Description :** 20 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 2 Pole/3 Wire, 250V, Blue

**Series Number :** 130150

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 320R6W



---

## Documents and Resources

### Drawings

[1301500059 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Wiring Devices
Series	130150
Description	20 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 2 Pole/3 Wire, 250V, Blue
Comments	IEC Configuration 309-1/309-2
IP Rating	IP67
NEMA Configuration	N/A
Product Name	Watertite
Specialty	Pin and Sleeve
Type	Receptacle
UPC	78678861337

#### Agency

UL	E145923
----	---------

#### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

#### Physical

Cord Type	N/A
Flange	Yes
Flip Lid	Yes
Gender	Female
Length	N/A

Lighted Connector	No
Locking Blade	Yes
Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on May 19, 2026