Part Number : 192030384
Product Description : Krimptite Temp-Term Butt Splice for 22-18 AWG Wire, 483°C (900° F), Loose Piece
Series Number : 19203
Status : Active
Product Category : Splices



Documents and Resources

Drawings

192030384_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19203
Description	Krimptite Temp-Term Butt Splice for 22-18 AWG Wire, 483°C (900° F), Loose Piece
Product Name	Krimptite
Style	High Temperature
Type	Butt Splice
UPC	822348424733

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel
Net Weight	0.761/g
Packaging Type	Carton
Temperature Range - Operating	483°C
Wire Insulation Diameter	3.60mm
Wire Size (AWG)	18, 20, 22

Downloaded from Arrow.com.