

LED, socket BA 9s, 24 Volt, green, LED



description

technical data

> general

Luminous element color	green
Collar shape	round
Operating temperature, min.	-30 °C
Operating temperature, max.	60 °C
Storage temperature, min.	-35 °C
Storage temperature, max.	100 °C
illuminated	Yes
Luminous elements	LED
Lamp socket	BA9s
Packaging unit	5 pcs.
net weight	3.8 g
MOQ order	5 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

> RAFI eCatalog

> mounting diameters

Outside dimension, length	25 mm
Outside dimension, width	10.95 mm
Outside dimension, height	10.95 mm
Collar dimension	9.8 mm

> electrical data

Operating voltage of the luminous element, max.	24 V
Voltage type	AC / DC
Operating current of the luminous element, max.	15 mA