



+ CABLE ASSEMBLIES

POWER CABLE ASSEMBLIES



✓ Active

TE CONNECTIVITY (TE)

CA,ET, 3POS, LONG PULL-TAB,NO DETECT

ELCON | ELCON Mini

2304886-1

TE Internal Number: 2304886-1

EU RoHS Compliant

EU ELV Compliant

Configuration Double-Ended

Shielded No

Cable Assembly Length (m) .25

Color Black

Operating Temperature Range (°C) -25 – 125

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

Cable AssY, ET 3POS, LONG PULL-TAB

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

ELCON Mini Power Interconnects QRG EN

PDF

English

Product Specifications

Product Specification

ELCON Mini,3-Position Cable-To-Board Power Connector System

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Shielded No
- Cable Assembly Type Power
- Connector Type (End A) Power Connector
- Connector Type (End B) Power Connector
- Product Type Cable Assembly
- Cable Assembly Category Power

Configuration Features

- Configuration Double-Ended
- Number of Positions 3

Body Features

- Color Black

Housing Features

- Housing Material Thermoplastic
- Housing Color Black

Dimensions

- Cable Assembly Length (m) .25
- Wire Size (AWG) 12

Usage Conditions

Operating Temperature Range (°C) -25 – 125

Industry Standards

UL Rating Listed

UL Flammability Rating UL 94V-0

Statement of Compliance

Statement of Compliance
PDF