Product Line

- Single Pair Ethernet
- ZConnect
- Ceres
  - Accessory
  - Large Size
  - Macro Size
  - Middle Size
  - Mini Size
  - Others (GBD)
  - Others (MAB)
  - Others (PLD)
  - Standard Size
- X-Lok
- M Series
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





CD-14PMMM-SL7A03

Operating Temperature: -20°C ~ +80°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: PVC

Certificate: N/A

You must login first for view the price

Quantity − 1 +

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search



Ceres, Middle Size,...
1CD-14BFFM-SL6A01
-20°C ~ +80°C



Ceres, Middle Size,...
ACD-14AFFM-SL7A01
-20°C ~ +80°C



Ceres, Middle Size,...
ACD-14AFFM-SL7A02
-20°C ~ +80°C



Ceres, Middle Size,...
ACD-14AFFM-SL7A03
-20°C ~ +80°C

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **5A**	Connector Type **Receptacle With Cable**
Shielded **Plastic, Non-shielded**	No. of Contacts **14**
Connector Gender **Male**	Backshell **Straight**
Mating Style **Screw Thread**	IP Rating **IPX7**
Assembly Style **N/A**	

More Options

People Also Bought

Downloaded from Arrow.com.