

NUMBER

C-166276-166277

LONG PIN ASS'Y
166276-1

CONSISTS OF:

- 1 PIN, KEYING
- 1 LOCK WASHER
- 1 NUT

1 FLAT WASHER

COMPONENTS ARE
PACKAGED UNASSEMBLED1.122
(28,5).728
(18,5)137 DIA
(3,5).026
(,3,2).020
(,5).032
(,8)

.040 (1,0)

.040 (1,0)

.728
(18,5).666
(16,9)1.122
(28,5).020
(,5).126
(3,2)137 DIA
(3,5)

30°

30°

30°

4-40 UNC THREAD
WIDTH ACROSS FLATS: .197 (5,0)
WIDTH ACROSS CORNERS: .223 (5,7).015
(,4).156
(4,0)

.197 (5,0) DIA

.125 (3,2) DIA

.032 (,8)

.197 (5,0) DIA

.141 (3,6) DIA

.156
(4,0) REF.WIDTH ACROSS FLATS: .197 (5,0)
WIDTH ACROSS CORNERS: .223 (5,7)

4-40 UNC THREAD

LONG SOCKET ASS.
166277-1

CONSISTS OF:

- 1 SOCKET, LONG
- 1 LOCK WASHER
- 1 NUT
- 1 FLAT WASHER

COMPONENTS ARE
PACKAGED UNASSEMBLED.

CUSTOMER COPY FOR REFERENCE ONLY

©1979 BY AMP-HOLLAND N.V. ALL RIGHTS
RESERVED A-MP PRODUCTS COVERED BY
PATENTS AND/OR PATENTS PENDING.AMP-HOLLAND N.V.
's-Hertogenbosch

166277-1	STAINL STEEL	PASSIVATED
166276-1	STAINL STEEL	PASSIVATED

WIRE RANGE	INSUL RANGE	FIRST USED
—	—	164706/164720

ORDER NO.	MATERIAL	PLATING
-----------	----------	---------

SCALE	SIZE	NO	REV
3:1	A	C-166276-166277	B

DATE	DE	DATE
8-5-79		
DATE	APP	DATE
8-5-79		

NAME LONG PIN/LONG SOCKET KEYING
FOR "H.D.R."-SERIES

DIMENSIONS IN (MM) DO NOT SCALE PRINT