

PART NO.	EXT. DIM. "A"	MOUNTING METHOD	INT. SECTION IN² [MM²]
*RX1313-0	.49 [12.5]	SCREW	.171 [110.0]
*RX1313-4		ADHESIVE	
RX1616-0	.63 [16.0]	SCREW	287 [185.0]
RX1616-4		ADHESIVE	
RX2020-0	.79 [20.0]	SCREW	.496 [320.0]
RX2020-4		ADHESIVE	
RX2525-0	.98 [25.0]	SCREW	.775 [500.0]
RX2525-4		ADHESIVE	
RX3030-0	1.18 [30.0]	SCREW	1.116 [720]
RX3030-4		ADHESIVE	
RX4040-0	1.57 [40.0]	SCREW	2.046 [1320.0]
RX4040-4		ADHESIVE	
RX5050-0	1.97 [50.0]	SCREW	3.162 [2040.0]
RX5050-4		ADHESIVE	

*ONLY ON THESE TWO PARTS,
ALL HOLES HAVE THE SAME ORIENTATION

NOTES:

1. MATERIAL: POLYPROPYLENE (RMS-177).
2. COLOR: GRAY RAL 7040.
3. SHR CAT INSTALLATION TOOL SERIES CAN BE USED FOR QUICK HARNESS ASSEMBLY
4. DOUBLE SIDED ADHESIVE TAPE (RMS-93).
5. SCREW MOUNT CHANNEL IS UL LISTED

TITLE: CHANNEL, FLEXIBLE (RICHFLEX)					DWG IN IN [MM] FINAL		PRINT TYPE
CREATED USING SOLIDWORKS		FILE #: RX XXXX-X	DWN: SM	APP: -	PART #		
TOLERANCES UNLESS NOTED XX±.010 XXX±.005 FRAC = ±1/64 ANG = ±1°		SHEET: 1 OF 2	SHEET SIZE: A	DT: 01/04/05	CHKD: -	SEE TABLE CA	
RE: RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060							
G	REV.	REMOVED V-0 MATERIAL, SEE CO 200625	SK	02/16/11			
F		SEE CO 200072	SK	11/28/07			
E		SEE ECN #903 FOR CHANGES	SM	01/04/05			
-		SEE ENGINEERING FOR REV A-D	--	----			
		DESCRIPTION	ENGR.	DATE			