

- Quick Links
- Cross reference
- RoHS/LF P/N Search
- Industry Standards
- Alphabetical List
- Documentation
- 3D model search
- Customer drawing search
- Multi Selection Search
- Search by category

Start > Search=10127817-121LF* > 10127817-121LF

10127817-121LF

10127817-121LF - Minitek® Pwr4.2 : Minitek® Pwr4.2 Female Terminal, Phosphorus Bronze, Tin plating, AWG #16-#22, Post-Plated



Customer drawing

Product Environmental Compliance Report

ACTIVE

RoHS Compliant



Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Specifications

Download document

Dimensional General Electrical Mechanical Physical Other Features

Dimensional

Pitch4.2

General

Number of contacts1

Series10127817

Electrical

Withstanding Voltage1500 Vac, No breakdown.
Current leakage < 5mA

Current ratingUP to 9 Amps

Resistance (Contact)10 milliohm max.

Resistance (Insulation)1000M ΩMin

Voltage rating600V

Mechanical

Durability (Mating cycles)30 Cycles

Insertion force14.7N max.

Withdrawal Force1 N min.

Physical

Material (Contact)PhBr

Plating (Contact area)Tin

Temperature (Range)-40°C to +105°C

Other Features

Packaging (Type)Paper Reel

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.