TE Connectivity: Every Connection Counts
© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

CONNECTOR HOUSINGS



✔ Active

3D PDF

TE CONNECTIVITY (TE)

DYNAMIC 1200D TAB HSG 6P F/H NATURAL Y

Dynamic Series | Dynamic 1000 Series

2-1939796-3

TE Internal Number: 2-1939796-3

Always EU RoHS/ELV Compliant

Connector System **Wire-to-Wire**

Centerline **2.5 mm [.098 in]**

Row-to-Row Spacing **3.3 mm [.129 in]**

Number of Positions **6**

Number of Rows **2**

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Catalog Pages/Data Sheets

1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH
PDF
English

Product Specifications

Product Specification

DYNAMIC CONNECTOR D1000 SERIES TIN PLATE
PDF
Japanese

DYNAMIC CONNECTOR D1000 SERIES GOLD PLATING
PDF
Japanese

Application Specification

CRIMPING DYNAMIC D1000 SERIES CONTACT
PDF
Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

Instruction Sheet, The Extraction Tool For Dynamic 1000 Series Connector
PDF
Japanese

Downloaded from Arrow.com.

Please review product documents or contact us for the latest agency approval information.

Product Type Features	Connector System	**Wire-to-Wire**
	Row-to-Row Spacing	**3.3 mm [.129 in]**
	Connector Style	**Plug**
	Sealed	**No**
	Applies To	**Wire/Cable**
	Series Number	**1000**
	Glow Wire Rating	**Standard Part - Not Glow Wire**
	Product Type	**Connector**
	Connector Type	**Housing**
Configuration Features	Number of Positions	**6**
	Number of Rows	**2**
	Selectively Loaded	**No**
	Preloaded	**No**
Electrical Characteristics	Operating Voltage	**250 VAC [250 VDC]**
Body Features	Sealable	**No**
Contact Features	Contact Type	**Tab**
	Contact Layout	**Matrix**
	Shunts/Shorting Bars	**Without**
	Multiple Contact Types	**Without**
Mechanical Attachment	Panel Mount Retention	**Without**
Housing Features	Centerline	**2.5 mm [.098 in]**
	Housing Material	**Polyester GF**
	Housing Color	**Natural**
Dimensions	Length	**10.1 mm [.397 in]**
	Height	**21 mm [.826 in]**

Downloaded from Arrow.com.

	Width	**11.3 mm [.444 in]**
Usage Conditions	Operating Temperature Range	**-55 – 105 °C [-67 – 221 °F]**
Operation/Application	Halogen Free	**Yes**
	For Use With	**Receptacle Housing**
Industry Standards	CSA Rating	**Certified**
	CSA File Number	**LR7189**
	UL Rating	**Recognized**
	CSA Certified	**Yes**
	VDE Tested	**No**
	UL File Number	**E28476**
	Agency/Standard	**CSA, UL**
	UL Flammability Rating	**UL 94V-0**
Packaging Features	Packaging Quantity	**100**
	Packaging Method	**Bag**
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	

Downloaded from Arrow.com.