

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982660552](#)
Status: **Active**
Overview: Premo-Flex Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 50 Circuits, 0.229m Cable Length, Tin(Sn) Plating

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-98266-001-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-98266-001-001 (PDF)	

General

Product Family	Cable
Series	98266
Comments	Contacts on opposite sides, Type D, Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Literature Order No	987650-6631
Product Name	Premo-Flex FFC Jumper
UPC	756054770061

Physical

Cable Length	0.229m
Circuits (Loaded)	50
Circuits (maximum)	50
Net Weight	3.670/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98266-001-001
Product Specification	PS-98266-001-001
Sales Drawing	SD-98266-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

China RoHS

Search Parts in this Series

98266 Series

Mates With

Easy-On FFC/FPC Connector:

[541045033](#) , [541325033](#) , [5019515000](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION