




PRODUCT NUMBER	PITCH
Klxx30x200J0G	3.81 mm



Material:

- Item① Terminal housing: Thermoplastic (UL94 V-0)
- Item② With flange screw: Steel Zinc plated, M2.5"/+/-"

Electrical cULus

- Voltage rating: 160V
- Current rating: 8A
- Wire range: 1.0~1.2mm²
- Withstanding Voltage: 1.32KV
- Corresponding female crimp contacts: A0 3.81 series

N=number of poles

Dim A=(N-1)×3.81+14.20
Dim B=(N-1)×3.81
Dim C=(N-1)×3.81+4.60
Dim D=(N-1)×3.81+9.0

Poles	2P~6P	7P~12P	13P~18P	19P~24P
Dim A	±0.20	±0.25	±0.30	±0.35
Dim B	±0.15	±0.20	±0.25	±0.30
Dim C	±0.20	±0.25	±0.30	±0.35
Dim D	±0.20	±0.25	±0.30	±0.35

PART NO.: Kl xx 30 x 2 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
02	2 poles	0 Black (RAL9005)	
03	3 poles	2 Red (RAL3001/D)	
...	...	3 Orange(RAL2011/P)	
24	24 poles	4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family			
ltr ecn no dr date				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK			
				tolerances unless otherwise specified		MM	title			
				angles	X.±0.5		TERMINAL BLOCK			
				dr	X.X±0.3		PLUGGABLE PLUG, WITH FLANGE, CRIMP CONNECTION			
				enr	X'±1°		scale			
				dr	EVIN ZHONG	050414	FCI			
				enr	EVIN ZHONG	050414				
				chr	HANKE FENG	050414				
				appd	SHI JUN	050414	type			
sheet index				revision	A		CUSTOMER Drawing			
sheet 1										