



Languages ▼

Registered users

Login

Password

GO

Forgot password?

Register Now

search: by P/N or text

GO

PRODUCTS

CONNECTION TYPE

PRODUCT MICROSITES

APPLICATIONS

Home

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=TJ10115300J0G* > TJ10115300J0G

TJ10115300J0G

TJ10115300J0G -
Terminal Blocks :
Pluggable plug,
3.5mm pitch,
horizontal wire-
inlet, 10 position



Specifications

Download document

Mechanical General Physical Electrical Dimensional Approvals / Certifications

Mechanical

Number of mating cycles 200

General

Gender Female plug

Packaging Box

Product Type Screw Pluggable System

Series TJ

Number of Positions 10

Physical

Color (Housing) Green

Conductor entry angle 0°

Material (Housing) Thermoplastic UL94V-0

Terminal material Phosphor bronze

Terminal plating Tin

Screw material Steel

Screw plating Zinc

Clamp material Brass

Clamp plating Nickel

Connection Type Screw connection

Temperature (Operating - range) -40 to 115 Celcius

Torque 3.0 Lb-in

Electrical

Withstanding Voltage 1.6 kV

Current rating 10 A

Voltage rating 300 V

Dimensional

Strip length (Wire) 6 to 7 mm

Solid wire size (AWG) 16 to 28

Solid wire size (mm2) 1.5

Stranded wire size (AWG) 16 to 28

Stranded wire size (mm2) 1.5

© FCI 2014 All Rights Reserved | Privacy Policy | Terms of Use