



Representative Image

Catalog No. 256-31426-6SPH

Description: CU TP 2HL LUG 90D STD 14-10 No10B C

UPC No 786210279244

Home > Connectivity & Grounding > Color Keyed / Blackburn > Cable or wire lug

Copper Two-Hole Lug, 90 Degree Standard Barrel, Blind End, Peep Hole, Max 35kV, Wire Size 14-10 AWG, #10 Bole Size, 5/8 - 3/4 Inch Hole Spacing, Tin Plated, Die Color Code 'C' Nest, Die Code ERG2002 ERG2005

Descriptors

Category	Cable or wire lug
----------	-------------------

Specifications

Cable Size	14-10 AWG
Number Of Holes	2
Voltage Rating	35 kV
Insulation	None
Material	Copper

Classifications

Brand Name	Color Keyed / Blackburn
Standard	UL E9809 UL E9809

Dimensions

Stud Size	5/8-3/4 in
-----------	------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	90°
Slender flange model	N
Insulated	N
With sight-hole	Y
Material	Copper

by ABB

ETIM	EC001051 Tube cable lug for copper conductors
Surface protection	Tinned
Number of mounting holes	2
AWG size	Other